



gentec-e)

QE50LP-S-MB-D0

Pyroelectric detector for laser energy measurement up to 15 J.



PRODUCT FAMILY KEY FEATURES

MODULAR CONCEPT

Increase the power capability of your detector: 2 different cooling modules

LOW NOISE LEVEL

10 µJ for the MB coating

QED ATTENUATOR AVAILABLE

Measure up to 5X higher energies. Available with optional calibration, all wavelengths between 532 & 1064 nm, or single wavelength. Read mo

HIGH REPETITION RATE OPTIONS

- QE-MB: 200 Hz (standard)
- QE-MB: 500 Hz (upon request)
- QE-MT: 4 000 Hz (standard)

TEST TARGET INCLUDED With the MB models

SMART INTERFACE

Containing all the calibration data

COMPATIBLE STAND

STAND-D-233

SPECIFICATIONS

MEASUREMENT CAPABILITIES

Spectral range ¹	0.193 - 20 μm
Typical rise time	900 µs
Repeatability	<0.5%
Maximum repetition frequency	200 Hz
Maximum measurable energy ²	15 J
Noise equivalent energy ³	10 µJ
Maximum pulse width	675 µs
Energy calibration uncertainty	±3 %

1. For the calibrated spectral range, see the user manual.

At 1064 nm, 7 ns, 10 Hz. Increasing pulse width increases maximum measurable energy.
Nominal value. Actual value depends on electrical noise in the measurement system.

DAMAGE THRESHOLDS

Maximum average power density ¹	10 W/cm ²
Maximum energy density ²	0.6 J/cm ²
Maximum power	10 W
1. May vary with wavelength and average power.	

2. At 1064 nm, 7 ns, 10 Hz. May vary with wavelength and pulse width.

PHYSICAL CHARACTERISTICS

Cooling	Convection
Aperture width	50 mm
Aperture height	50 mm
Absorber	МВ
Dimensions	75H x 75W x 15D mm





Instrument Expert Original factory packaging www.dorgean.com

Weight	0.21 kg
ORDERING INFORMATION	
QE50LP-S-MB-D0	200479
QE50LP-S-MB-INE-D0	
QE50LP-S-MB-INT-D0	202750
QE50LP-S-MB-IDR-D0	203280

Specifications are subject to change without notice. Refer to the user manual for complete specifications.

INTERESTED IN THIS PRODUCT?

GET A QUOTE

Find your local sales representative at gentec-eo.com/contact-us